## Ceiling DocCam RS232



## On/Off Codes

**Description:** This document describes the added Ceiling Doc Cam On/Off codes. The Ceiling

DocCam must be labeled Rev 2.3 or higher for these codes to work.

Code:

All Commands must be followed by an ASCI return character RS232: 4800bps, Even parity, 8bit data, 1stop bit

Please check the manual for complete RS232 information.

Ceiling DocCam ON :WFCVL01

Ceiling DocCam OFF :WFCVL02

NOTE: This code only turns off the Camera functions. The main board still retains power enabling the On command from both RS232 and IR